

Catalog Number: SP20/PG16/M
Product ID: 7TCA296020R0170
EAN Number: 05020963009044
Status: Active

Nickel Plated Brass Straight Compression Fitting with Swivel External Thread, Nominal Conduit Size 20 Millimeters, PG Thread Size PG16

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Conduit Fitting with PG Threads
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	NC 20mm
Material	Brass
Finish	Nickel Plated
Color	Metallic
Connection	Straight
Cable Entry	PG16 Thread

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	20mm
Degree of protection (IP) conduit dependant	IP65-IP65
Model	Straight
Revolving thread	Y
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	Other
Thread connection size	PG16
One-piece	Y
Material housing	Brass
Surface protection	Nickel-plated
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UL	N
Approved in combination with protective conduit FI	N
Operating temperature	-50-+150°C

Packaging

Outer Quantity	10
Outer Dimensions (inches)	1x1x1
Weight Uom	0.14 lbs. Each

Header

3D Model	Available on Website
----------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

T&B Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com