



Representative

Catalog Number: SPB20/M20/B
Product ID: 7TCA296040R0127
EAN Number: 05020963002779
Status: Active

Nickel Plated Brass Straight Fitting with Swivel External Thread, Nominal Conduit Size 20 Millimeters, IP54 Rating, Metric Thread Size M20

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Conduit Fitting with Metric Threads
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	1/2 Inch
Material	Brass
Finish	Nickel Plated
Color	Metallic
Connection	Straight
Cable Entry	M20 Thread

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	20mm
Degree of protection (IP) conduit dependant	IP54-IP54
Model	Straight
Revolving thread	Y
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	Metric
Thread connection size	M20 x 1.5
One-piece	Y
Material housing	Brass
Surface protection	Nickel-plated
Thread length	10mm
Total length	40mm
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UL	N
Approved in combination with protective conduit FI	N
Operating temperature	-50-+300°C

Packaging

Outer Quantity	10
Outer Dimensions (inches)	1x1x1
Weight Uom	0.11 lbs. Each

For further technical assistance, please contact us...

8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com