

**Catalog Number:** SPB50/M50/B  
**Product ID:** 7TCA296040R0163  
**EAN Number:** 05020963008702  
**Status:** Active



Other

1-1/2 Inch Nickel Plated Brass Straight Fitting with Swivel External Thread, IP54 Rating, Metric Thread Size M50

### North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Conduit Fitting with Metric Threads
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	1-1/2 Inch
Material	Brass
Finish	Nickel Plated
Color	Metallic
Connection	Straight
Cable Entry	M50 Thread

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	50mm
Nominal size in inch	1 1/2 inch
Degree of protection (IP) conduit dependant	IP54-IP54
Model	Straight
Revolving thread	Y
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	Other
Thread connection size	M50 x 1.5
One-piece	Y
Material housing	Brass
Surface protection	Nickel-plated
Thread length	14mm
Total length	57.9mm
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UL	N
Approved in combination with protective conduit FI	N
Operating temperature	-50-+300°C

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	1x1x1
Weight Uom	0.81 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)