

**Catalog Number:** SPL16/M16/A  
**Product ID:** 7TCA296030R0091  
**EAN Number:** 05020963001024  
**Status:** Active



3/8 Inch Nickel Plated Brass Liquid Tight Straight Fitting with Fixed External Threads, Metric Thread Size M16

Other

### North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Liquid Tight Non-Metallic Fitting
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	3/8 Inch
Material	Brass
Finish	Nickel Plated
Color	Metallic
Connection	Straight
Cable Entry	M16 Thread

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	16mm
Nominal size in inch	3/8 inch
Degree of protection (IP) conduit dependant	IP67-IP67
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	Metric
Thread connection size	M16 x 1.5
One-piece	Y
Material housing	Brass
Surface protection	Nickel-plated
Thread length	13mm
Total length	33mm
Total height	24mm
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UL	N
Approved in combination with protective conduit FI	N
Operating temperature	-65-+150°C

### Packaging

Outer Quantity	10
Outer Dimensions (inches)	1x1x1
Weight Uom	0.08 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)