

Catalog Number: **SPL32/100/M**
Product ID: 7TCA296030R0234
EAN Number: 05020963013058
Status: Active

Nickel Plated Brass Liquid Tight Straight Swivel Fitting with External Thread, Nominal Conduit Size 32 Millimeters, NPT Thread Size 1 Inch

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	32mm
Degree of protection (IP) conduit dependant	IP66-IP69
Model	Straight
Revolving thread	Y
Construction type	External thread
Thread type	NPT
Thread connection size	Other
Material housing	Brass
Surface protection	Nickel-plated
Approved in combination with protective conduit UL	Y
Operating temperature	-65-+150°C

Packaging

Outer Quantity	2
Outer Dimensions (inches)	1x1x1
Weight Uom	0.33 lbs. Each

Header

3D Model	Available on Website
----------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

T&B Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com