

**Catalog Number:** SPL32/PG29/M  
**Product ID:** 7TCA296030R0264  
**EAN Number:** 05020963000683  
**Status:** Active



Representative

Nickel Plated Brass Liquid Tight Straight Swivel Fitting with External Thread, Nominal Conduit Size 32 Millimeters, PG Thread Size PG29

### North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Liquid Tight Non-Metallic Fitting
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	1 Inch
Material	Brass
Finish	Nickel Plated
Color	Metallic
Connection	Straight
Cable Entry	PG29 Thread

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	32mm
Degree of protection (IP) conduit dependant	IP66-IP69K
Model	Straight
Revolving thread	Y
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	Other
Thread connection size	PG29
One-piece	N
Material housing	Brass
Surface protection	Nickel-plated
Thread length	12mm
Total length	42mm
Total height	42mm
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UL	Y
Approved in combination with protective conduit FI	N
Operating temperature	-65-+150°C

### Packaging

Inner Quantity	2
Outer Quantity	100
Outer Dimensions (inches)	1x1x1
Weight Uom	0.41 lbs. Each

### Header

3D Model

Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)