



Representative

**Catalog Number:** SPL63/200/M  
**Product ID:** 7TCA296030R0312  
**EAN Number:** 05020963789571  
**Status:** Active

Nickel Plated Brass Liquid Tight Straight Swivel Fitting with External Thread, Nominal Conduit Size 63 Millimeters, NPT Thread Size 2 Inch

### North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Liquid Tight Non-Metallic Fitting
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	2 Inch
Material	Brass
Finish	Nickel Plated
Color	Metallic
Connection	Straight
Cable Entry	2 Inch NPT Thread

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	63mm
Degree of protection (IP) conduit dependant	IP66-IP69K
Model	Straight
Revolving thread	Y
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	Y
Material housing	Brass
Surface protection	Nickel-plated
Total length	72.5mm
Total height	70mm
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UL	Y
Approved in combination with protective conduit FI	N
Operating temperature	-65-+150°C

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	1x1x1
Weight Uom	1.24 lbs. Each

For further technical assistance, please contact us...

860 Ridge Lake Blvd.  
Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)