



Family

**Catalog Number:** SVN4-29.20  
**Product ID:** 7TAA292640R0006  
**UPC Number:** 78620997503  
**EAN Number:** 07630030275142  
**Status:** Active

Flat Gasket, PG Thread - Fits to Thread Size PG 29

### North American Specifications (UNSPSC)

UNSPSC	31161818 Seal washers
IGCC	2897 Seal washers
Brand Name	PMA
Type	Flat Gasket
Application	Sealing Fittings with Polyamide or Metal Threads
Material	NBR Rubber
Thickness	1.5 Millimeters
Outside Diameter	48 Millimeters
Inside Diameter	PG29
Color	Blue
Temperature Rating	-50 to +250 Celsius

### European Specifications (ETIM)

ETIM	EC001181 Sealing ring
Model	Flat sealing
Outer diameter	48mm
Inner diameter	37mm
Thickness	1.5mm
Material	Rubber
Fitting for thread size PG	29

### Packaging

Inner Quantity	20
Outer Quantity	2400
Outer Dimensions (inches)	15.748x11.811x8.661
Weight Uom	0.01 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet Canada Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)