



Family

Catalog Number: SVN4-G07.20
Product ID: 7TAA292640R0015
UPC Number: 78620997486
EAN Number: 07630030275050
Status: Active

Flat Gasket, Gas/NPT Thread - Fits to Thread Size Gas/NPT 1 1/4 Inch

North American Specifications (UNSPSC)

UNSPSC	31161818 Seal washers
IGCC	2897 Seal washers
Brand Name	PMA
Type	Flat Gasket
Application	Sealing Fittings with Polyamide or Metal Threads
Material	NBR Rubber
Thickness	1.5 Millimeters
Outside Diameter	53 Millimeters
Inside Diameter	1-1/4 Inch NPT
Color	Blue
Temperature Rating	-50 to +250 Celsius

European Specifications (ETIM)

ETIM	EC001181 Sealing ring
Model	Flat sealing
Outer diameter	53mm
Inner diameter	41.9mm
Thickness	1.5mm
Material	Rubber
Fitting for thread size NPT	1.25

Packaging

Inner Quantity	20
Outer Quantity	1500
Outer Dimensions (inches)	15.748x11.811x8.661
Weight Uom	0.01 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet Canada Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com