



Family

Catalog Number: SVN4-M20/02.50
Product ID: 7TAA292640R0023
UPC Number: 78620920893
EAN Number: 07630030274978
Status: Active

Flat Gasket, Metric Thread - Fits to Thread Size M20x1.5, Large AD

North American Specifications (UNSPSC)

UNSPSC	31161818 Seal washers
IGCC	2897 Seal washers
Brand Name	PMA
Type	Flat Gasket
Application	Sealing Fittings with Polyamide or Metal Threads
Material	NBR Rubber
Thickness	1.5 Millimeters
Outside Diameter	33 Millimeters
Inside Diameter	M20x1.5
Color	Blue
Temperature Rating	-50 to +250 Celsius

European Specifications (ETIM)

ETIM	EC001181 Sealing ring
Model	Flat sealing
Outer diameter	33mm
Inner diameter	20mm
Thickness	1.5mm
Material	Rubber
Fitting for thread size metric	20

Packaging

Inner Quantity	50
Inner Dimensions (inches)	8x3.1x3.75
Outer Quantity	5000
Outer Dimensions (inches)	15.748x11.811x8.661
Weight Uom	0.01 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet Canada Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
 www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com