



Actual

Catalog Number: TC88
Product ID: 7TAG009710R0008
UPC Number: 78621082615
EAN Number: 05414363059363
Status: A

Mechanical-Locking Routing Clamp, Natural Nylon 6.6 for Temperatures up to 85 Celsius (185 F), Length of 19.1mm (0.75 Inches), Width of 12.7mm (0.50 Inches), Height of 40.5mm (1.59 Inches), Mounting Hole Size of 6.35mm (0.25 Inches), Clip or Glue Mounting Method

- Clamp acts as a retainer during wire routing, and as a permanent clamp when desired.

North American Specifications (UNSPSC)

UNSPSC	39121705 Cable clamp and staple
IGCC	5049 Cable clamp and staple
Type	Mechanical-Locking Routing Clips
Special Features	Clamp acts as a retainer during wire routing, and as a permanent clamp when desired.
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Push Mount

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	19.1mm
Width	12.7mm
Height	40.5mm
Type of fastening	Other
Material	Plastic
Material quality	Polyamide PA
Colour	Natural colour

Packaging

Inner Quantity	100
Outer Quantity	1000
Outer Dimensions (inches)	17.5x12.7x6.4
Weight Uom	3.13 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------