



Actual

Catalog Number: TC828-TB
Product ID: 7TAG009880R0015
UPC Number: 78621082637
EAN Number: 05414363075073
Status: A
Replacement Catalog: TC5828

Four-Way Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 22.48mm (0.885 Inches), Width of 10.16mm (0.40 Inches), Height of 3.8mm (0.15 Inches), Screw Mounting Method, #8 Hex Head Screw, Mounting Hole Diameter of 4.3mm (0.17 Inches), Bulk Pack

- These mounting bases can be used to tie bundles running parallel or perpendicular to length of base.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	These mounting bases can be used to tie bundles running parallel or perpendicular to length of base.
Number Of Entries	2
Mount Size	#8
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	22.48mm
Width	10.16mm
Height	3.8mm
Suitable for cable tie width to	4.8mm
Type of fastening	Other
Diameter mounting hole	4.3mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

Packaging

Inner Quantity	1000
Outer Quantity	10000
Outer Dimensions (inches)	13x10.8x8.9
Weight Uom	1.25 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US Available on Website