

**Catalog Number:** CPO500-C-C  
**Product ID:** 7TAA017310R0207  
**UPC Number:** 78621083531  
**Status:** A



Actual

Thin-Wall Heat Shrinkable Tubing, Clear Cross-Linked Polyolefin, 1/2 Inch, Shrink Ratio 2:1, Length 100 Feet, Operating Temperature -55 to 135 Degrees Celsius, Non-Lined

- Flame-retardant, cross-linked polyolefin.
- Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C; MIL-DTL-23053/5 Class 1&2; AMS 3636 & 3637; DEF STAN 59-97, Issue 3, Type 2a

### North American Specifications (UNSPSC)

|                  |   |
|------------------|---|
| UNSPSC           | 39121723 Heat shrinkable tube             |
| IGCC             | 5073 Heat shrinkable tube                 |
| Type             | Thin-Wall Heat Shrinkable Tubing          |
| Special Features | Flame-retardant, cross-linked polyolefin. |
| Shrink Ratio     | 2:1                                       |
| Thickness        | Thin                                      |
| Length           | 100 ft                                    |
| Color            | Transparent                               |

### European Specifications (ETIM)

|                                   |                        |
|-----------------------------------|------------------------|
| ETIM                              | EC000217 Shrink tubing |
| Type                              | Heat-shrink            |
| Model                             | Thin-walled            |
| Shrink rate                       | 2:1                    |
| Inner diameter before heat-shrink | 12.7mm                 |
| Inner diameter after heat-shrink  | 6.35mm                 |
| Nominal diameter inch             | 1/2 inch               |
| Wall thickness after shrinking    | 0.762mm                |
| Length                            | 30.48m                 |
| Operation temperature             | -55-+135°C             |
| Colour                            | Transparent            |
| Material                          | Polyolefin (PO-X)      |
| Halogen free                      | N                      |
| With inner glue                   | N                      |
| Printable                         | N                      |
| UL approval                       | Y                      |

### Packaging

|                           |                |
|---------------------------|----------------|
| Outer Quantity            | 1              |
| Outer Dimensions (inches) | 13.3x13.3x3.9  |
| Weight Uom                | 2.44 lbs. Each |

### Documents / Support Tools

|                                   |                      |
|-----------------------------------|----------------------|
| Technical Drawing / Data Sheet US | Available on Website |
| Catalog Page                      | Available on Website |