



Actual



Actual

**Catalog Number:** 259-I  
**Product ID:** 7TAA106070R0011  
**UPC Number:** 78620989540  
**EAN Number:** 05414363449423  
**Status:** A

Squeeze Connector, Straight, Trade Size 2 Inch, Knockout Size 2 Inch, Cable Range 2.313 to 2.500 Inch, Insulated, Throat, Malleable Iron

#### North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	T&B Squeeze Connectors Will Fit Every Size of Armored Cable, Leaded Cable and Flexible Conduit
Application	For Use with Armored Cable and Flexible Metal Conduit
Standard	UL E23018, CSA 2884
Size	2 Inch
Conductor Range	2.313 to 2.500 Inch
Material	Malleable Iron
Finish	Zinc Plated
Color	Metallic
Insulation	Insulated Throat

#### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Thread length	17.46mm

#### Packaging

Inner Quantity	5
Inner Dimensions (inches)	9.75x6.75x4.75
Outer Quantity	10
Outer Dimensions (inches)	9.81x7.06x10.06
Weight Uom	110 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000408
--------------------------------	------------