



Actual

Catalog Number: 279
Product ID: 7TAA106070R0031
UPC Number: 78621000279
Status: A

Squeeze Connector, 90 Degree Bend, Trade Size 3/4 Inch, Knockout Size 3/4 Inch, Cable Range 0.875 to 1.000 Inch, Malleable Iron

North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	Cap Lifts off by Simply Loosening Screws Part Way, Only Two Screws to Tighten
Application	For Use with Armored Cable and Flexible Metal Conduit
Standard	UL E23018, CSA 2884
Size	3/4 Inch
Conductor Range	0.875 to 1.000 Inch
Material	Malleable Iron
Finish	Zinc Plated
Color	Metallic
Insulation	No

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/4 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Thread length	46.03mm
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Inner Quantity	10
Inner Dimensions (inches)	6x4.5x3
Outer Quantity	50
Outer Dimensions (inches)	21.6x5.4x7.1
Weight Uom	30.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website