



Actual

Catalog Number: CPO-A-250-48
Product ID: 7TAA017320R0018
UPC Number: 78621024733
EAN Number: 05415022347609
Status: Active

Thin-Wall Heat-Shrinkable Tubing for Cable Range 22 - 10 AWG, Expanded Diameter 1/4 inch, Length 48 inches, rated for 600 Volt, 125 degrees C, Material: Cross-linked polyolefin - Adhesive Lined, Black

- Adhesive lined for moisture-proof environmental seal.
- High 3:1 shrink ratio for covering irregularly shaped objects.

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Brand Name	Shrink-Kon
Type	Thin-Wall Heat-Shrinkable Tubing
Special Features	Adhesive lined for moisture-proof environmental seal.
Voltage Rating	600V
Thickness	Thin
Length	48 in
Color	Black

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	3:1
Inner diameter before heat-shrink	6.35mm
Inner diameter after heat-shrink	2.032mm
Nominal diameter inch	1/4 inch
Wall thickness after shrinking	1.27mm
Length	1.22m
Operation temperature	-55-+110°C
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	Y
Printable	N
UL approval	N

Packaging

Outer Quantity	25
Outer Dimensions (inches)	48x4.2x4.2
Weight Uom	5 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website