



Representative

**Catalog Number:** TC050X050AX  
**Product ID:** 7TAG009840R0004  
**UPC Number:** 78621058518  
**EAN Number:** 05414363057819  
**Status:** A

Four-Way Adhesive Mini Mounting Base, Black Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Weather and Ultraviolet Resistant, Length of 12.7mm (0.50 Inches), Width of 12.7mm (0.50 Inches), Height of 4.52mm (0.178 Inches), Slot Width of 5.59 (0.22 Inches), Self-Adhesive Mounting Method, Bulk Pack

- Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.

### North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.
Material	Nylon/Polyamide 6.6 Weather Resistant
Color	Black
Mounting	Adhesive/Screw
Operating Temperature	-40 to +185 F

### European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	12.7mm
Width	12.7mm
Height	4.52mm
Suitable for cable tie width to	3mm
Type of fastening	Self-adhesive
Material	Plastic
Material quality	Polyamide PA
Operating temperature	0-+65°C
Colour	Black

### Packaging

Inner Quantity	1000
Inner Dimensions (inches)	12x3x10
Outer Quantity	5000
Outer Dimensions (inches)	9.5x5x15.25
Weight Uom	1.25 lbs. per 1000

### Documents / Support Tools

Catalog Page	Available on Website
--------------	----------------------