



Family

**Catalog Number:** CHS100  
**Product ID:** 7TAA017340R0000  
**UPC Number:** 78621080341  
**Status:** A

Thin-Wall Heat-Shrinkable Tubing for Cable Range 4/0 - 300 MCM, Expanded Diameter 1 inch, Reel of 25 Feet, rated for 600 Volt, 125 degrees C, Material: Polyvinyl Chloride, Clear

- Clear shrink enables user to inspect die and crimp details after installation.
- Flexible PVC tubing is suitable for industrial and electronic applications.
- UL standard UL224, VW-1 Rated. CSA standard C22.2 no. 198.1 oft.

**North American Specifications (UNSPSC)**

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Thin-Wall Heat Shrinkable Tubing
Special Features	Clear shrink enables user to inspect die and crimp details after installation.
Shrink Ratio	2:1
Thickness	Thin
Length	25 ft
Color	Transparent

**European Specifications (ETIM)**

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	25.4mm
Inner diameter after heat-shrink	12.7mm
Nominal diameter inch	1 inch
Wall thickness after shrinking	1.016mm
Length	7.62m
Operation temperature	-30-+105°C
Colour	Transparent
Material	PVC
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y

**Packaging**

Outer Quantity	1
Outer Dimensions (inches)	12.75x8.75x6.5
Weight Uom	1 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------