



Actual

Catalog Number: TC101
Product ID: 7TAG009880R0000
UPC Number: 78621082240
EAN Number: 05414363057840
Status: A

Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 50mm (1.98 Inches), Width of 12.7mm (0.50 Inches), Height of 3.2mm (0.126 Inches), Screw Mounting Method, #10 Screw

- These nylon bases provide a mounting range for bundles from 1/4 to 4 inches in diameter. One mounting hole is slotted to permit adjustment of the bundle position up to the time of actual bundle installation.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	These nylon bases provide a mounting range for bundles from 1/4 to 4 inches in diameter. One mounting hole is slotted to permit adjustment of the bundle position up to the time of actual bundle installation.
Mount Size	#10
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	50mm
Width	12.7mm
Height	3.2mm
Suitable for cable tie width to	4.8mm
For maximum bundle diameter	1mm
Type of fastening	Other
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

Packaging

Inner Quantity	1000
Outer Quantity	10000
Outer Dimensions (inches)	18.5x11.1x8.1
Weight Uom	3.05 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------