



Actual

Catalog Number: HSMW4700-48
Product ID: 7TAA017210R0010
UPC Number: 78621024653
Status: Active

Medium-Wall Heat-Shrinkable Tubing for Cable Range , Expanded Diameter 4.7 inch, Length 48 inch, rated for 600 Volt, 90 degrees continuous use, Material: Cross-linked polyolefin with thermoplastic adhesive liner, Black

- More flexible than heavy-wall products. Seals and protects cable splices and terminations.
- Thermoplastic Adhesive Liner for complete environment protection and insulation.
- High resistance to impact and abrasion.

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Brand Name	Shrink-Kon
Type	Medium-Wall Heat-Shrinkable Tubing
Special Features	More flexible than heavy-wall products. Seals and protects cable splices and terminations.
Shrink Ratio	3:1
Length	48 in
Color	Black

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Medium-walled
Shrink rate	3:1
Inner diameter before heat-shrink	119.38mm
Inner diameter after heat-shrink	39.878mm
Nominal diameter inch	Other
Wall thickness after shrinking	2.794mm
Length	1.22m
Operation temperature	-55-+110°C
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	Y
Printable	N
UL approval	N

Packaging

Outer Quantity	5
Outer Dimensions (inches)	6x49x19
Weight Uom	15.63 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website
Safety Data Sheet (SDS) Global	SDS-00046-TB2

