



Actual

Catalog Number: TC116-0
Product ID: 7TAG009860R0002
UPC Number: 78621084376
EAN Number: 05414363058076
Status: A

Rivet-Mounted Base, Black Nylon 6.6 for Temperatures up to 85 Degrees Celsius, Length of 19.1mm (0.75 Inches), Width of 12.7mm (0.50 Inches), Height of 15mm (0.59 Inches), Rivet Mounted, #6 Clearance Hole up to 3.71 mm (0.146 Inches)

- Firmly locks into position when projecting pin is pushed into the mounting hole. Slip tie under base to attach bundle.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Self-Riveting Base
Special Features	Firmly locks into position when projecting pin is pushed into the mounting hole. Slip tie under base to attach bundle.
Mount Size	#6
Material	Nylon/Polyamide 6.6
Color	Black
Mounting	Push Mount
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	19.1mm
Width	12.7mm
Height	15mm
Type of fastening	Screw and rivet
Material	Plastic
Material quality	Polyamide PA
Colour	Black

Packaging

Inner Quantity	1000
Outer Quantity	10000
Outer Dimensions (inches)	13.3x10.9x11
Weight Uom	1.88 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------