



Representative

**Catalog Number:** TC150X150AX  
**Product ID:** 7TAG009840R0010  
**UPC Number:** 78621058501  
**EAN Number:** 05414363058267  
**Status:** A

Four-Way Mounting Base, Black Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Length of 38.1mm (1.5 Inches), Width of 38.1mm (1.5 Inches), Height of 7.4mm (0.290 Inches), Self-Adhesive/Screw Mounting Method, #8 Screw, Mounting Hole Size of 4.3mm (0.169 Inches), Bulk Pack

- Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.

**North American Specifications (UNSPSC)**

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.
Material	Nylon/Polyamide 6.6 Weather Resistant
Color	Black
Mounting	Adhesive/Screw
Operating Temperature	-40 to +185 F

**European Specifications (ETIM)**

ETIM	EC000449 Mounting base and -element for cable ties
Length	38.1mm
Width	38.1mm
Height	7.4mm
Suitable for cable tie width to	7.9mm
Type of fastening	Other
Diameter mounting hole	4.3mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	0-+65°C
Colour	Black

**Packaging**

Inner Quantity	500
Inner Dimensions (inches)	22x2x14
Outer Quantity	2500
Outer Dimensions (inches)	13x9x21
Weight Uom	7.5 lbs. per 1000

**Documents / Support Tools**

Technical Drawing / Data Sheet US Available on Website