

Catalog Number: CPO250-2-25
Product ID: 7TAA017310R0124
UPC Number: 78621092872
EAN Number: 05415022255485
Status: A



Thin-Wall Heat Shrinkable Tubing, Red Cross-Linked Polyolefin, 1/4 Inch, Shrink Ratio 2:1, Length 25-Foot Reel, Operating Temperature -55 to 135 Degrees Celsius, Non-Lined

- Flame-retardant, cross-linked polyolefin.
- Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C; MIL-DTL-23053/5 Class 1&2; AMS 3636 & 3637; DEF STAN 59-97, Issue 3, Type 2a

Actual

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Thin-Wall Heat Shrinkable Tubing
Special Features	Flame-retardant, cross-linked polyolefin.
Shrink Ratio	2:1
Thickness	Thin
Length	25 ft
Color	Red

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	6.35mm
Inner diameter after heat-shrink	3.302mm
Nominal diameter inch	1/4 inch
Wall thickness after shrinking	0.508mm
Length	7.62m
Operation temperature	-55-+135°C
Colour	Red
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y

Packaging

Outer Quantity	1
Outer Dimensions (inches)	xx
Weight Uom	40 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website