



Actual

**Catalog Number:** CPO750-S-25  
**Product ID:** 7TAA017310R0264  
**UPC Number:** 78621098689  
**Status:** A

Thin-Wall Heat Shrinkable Tubing, Green/Yellow Striped Cross-Linked Polyolefin, 3/4 Inch, Shrink Ratio 2:1, Length 25-Foot Reel, Operating Temperature -55 to 135 Degrees Celsius, Non-Lined

- Flame-retardant, cross-linked polyolefin.
- Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C; MIL-DTL-23053/5 Class 1&#amp;2; AMS 3636 &#amp; 3637; DEF STAN 59-97, Issue 3, Type 2a

### North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Thin-Wall Heat Shrinkable Tubing
Special Features	Flame-retardant, cross-linked polyolefin.
Shrink Ratio	2:1
Thickness	Thin
Length	25 ft
Color	Green/Yellow Striped

### European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	19.05mm
Inner diameter after heat-shrink	9.652mm
Nominal diameter inch	3/4 inch
Wall thickness after shrinking	0.762mm
Length	7.62m
Operation temperature	-55-+135°C
Colour	Green/yellow
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	13x6x13
Weight Uom	61.5 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website