



Catalog Number: MLP250-0-A
Product ID: 7TCA017310R0302
UPC Number: 78621080984
EAN Number: 05414363105084
Status: A



Heat Shrink Tubing, Flexible for High Specifications, UL/CSA Listed, Thin Wall, Shrink Ratio 2:1, 1/4 Inch/6.4mm Expanded Diameter, Black, 25 X 1.22M Lengths, CrossLinked Polyolefin, Item is Silicone, Cadmium and Lead Free

Actual

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Thin-Wall Heat Shrinkable Tubing
Shrink Ratio	2:1
Thickness	Thin
Length	4 ft ; 1.22 m
Continuous Operating Temperature	-67 to +212 F ; -55 to +100 C
Minimum Shrink Temperature	194 F ; 90 C
Flammability	Flame Retardant
Color	Black

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	6.4mm
Inner diameter after heat-shrink	3.2mm
Nominal diameter inch	1/4 inch
Wall thickness after shrinking	0.6mm
Length	1.22m
Operation temperature	-55-+135°C
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y

Packaging

Outer Quantity	25
Outer Dimensions (inches)	49.3x4.1x4.2
Weight Uom	2.56 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001470
Safety Data Sheet (SDS) Global	SDS-00046-TB2
Catalog	Available on Website