



Representative

Catalog Number: HSMW750-48
Product ID: 7TAA017210R0012
UPC Number: 78621024658
EAN Number: 05415022255560
Status: A

Medium-Wall Heat-Shrinkable Tubing for Cable Range , Expanded Diameter 3/4 inch, Length 48 inch, rated for 600 Volt, 90 degrees continuous use, Material: Cross-linked polyolefin with thermoplastic adhesive liner, Black

- More flexible than heavy-wall products. Seals and protects cable splices and terminations.
- Thermoplastic Adhesive Liner for complete environment protection and insulation.
- High resistance to impact and abrasion.

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Medium-Wall Heat Shrinkable Tubing
Special Features	More flexible than heavy-wall products. Seals and protects cable splices and terminations.
Voltage Rating	600 V
Length	48 in
Color	Black

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Medium-walled
Shrink rate	3:1
Inner diameter before heat-shrink	19.05mm
Inner diameter after heat-shrink	5.588mm
Nominal diameter inch	3/4 inch
Wall thickness after shrinking	2.032mm
Length	1.22m
Operation temperature	-55-+110°C
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	Y
Printable	N
UL approval	N

Packaging

Outer Quantity	25
Outer Dimensions (inches)	4x49x4
Weight Uom	16 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Safety Data Sheet (SDS) Global	SDS-00046-TB2

