

Catalog Number: CPO125-5-A
Product ID: 7TAA017310R0045
UPC Number: 78621083368
Status: Active



Thin-Wall Heat-Shrinkable Tubing for Cable Range 30 - 24 AWG, Expanded Diameter 1/8, Length 4 feet, rated for 600 Volt, 125 degrees C, Material: Cross-linked polyolefin - Non-lined, Green

- Flame-retardant, cross-linked polyolefin.
- Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C; MIL-DTL-23053/5 Class 1&2; AMS 3636 & 3637; DEF STAN 59-97, Issue 3, Type 2a

Actual

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Brand Name	Shrink-Kon
Type	Thin-Wall Heat-Shrinkable Tubing
Special Features	Flame-retardant, cross-linked polyolefin.
Shrink Ratio	2:1
Thickness	Thin
Length	4 ft
Color	Green

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	3.302mm
Inner diameter after heat-shrink	1.524mm
Nominal diameter inch	1/8 inch
Wall thickness after shrinking	0.508mm
Length	1.22m
Operation temperature	-55-+135°C
Colour	Green
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y

Packaging

Inner Quantity	25
Inner Dimensions (inches)	1x1x1
Outer Quantity	250
Outer Dimensions (inches)	10.5x4.5x51
Weight Uom	2 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website

