



Actual



Actual

Catalog Number: 249-I
Product ID: 7TAA106070R0001
UPC Number: 78620989541
EAN Number: 05414363449430
Status: A

Squeeze Connector, Straight, Trade Size 2-1/2 Inch, Knockout Size 2/12 Inch, Cable Range 2.812 to 3.062 Inch, Insulated Throat, Malleable Iron

North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	T&B Squeeze Connectors Will Fit Every Size of Armored Cable, Leaded Cable and Flexible Conduit.
Application	For Use with Armored Cable and Flexible Metal Conduit.
Standard	UL E23018, CSA 2884
Size	2-1/2 Inch
Conductor Range	2.812 to 3.062 Inch
Material	Malleable Iron
Finish	Zinc Plated
Color	Metallic
Insulation	Insulated Throat

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	2 1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Thread length	19.05mm

Packaging

Inner Quantity	1
Inner Dimensions (inches)	4.12x4.12x3.12
Outer Quantity	5
Outer Dimensions (inches)	16.5x4.5x4.75
Weight Uom	1.62 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000408
--------------------------------	------------