



Actual



Representative

Catalog Number: 2541-3
Product ID: 7TBD105020R0003
UPC Number: 78621058286
EAN Number: 05415022512595
Status: A

Multi-Hole Cord Connector with 3 Holes, Hub Size 1 Inch, Cord Diameter 0.290 to 0.310 Inch, Steel

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Multi-Hole Cord Connectors
Application	Ideal for Environments Where there is a Need to Run Multiple Cables Into an Enclosure and Space At the Enclosure is Limited.
Standard	UL E13938
Size	1 Inch
Conductor Range	0.290 to 0.310 Inch
Material	Steel
Color	Metallic
Temperature Rating	105 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1 inch
Thread length	19.83mm
Suitable for cable diameter	7.36-7.87mm
Material	Metal
Material quality	Steel
Colour	Natural colour
Model	Straight

Packaging

Inner Quantity	10
Outer Quantity	100
Weight Uom	35 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000082
Support/Tools	Available on Website

Header

3D Model	Available on Website
----------	----------------------