



Actual

**Catalog Number:** HSC30-250M  
**Product ID:** 7TAA017030R0001  
**UPC Number:** 78621096131  
**Status:** A

Heat Shrink End Cap Cable Range #3/0 - 250 MCM

### North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Brand Name	Shrink-Kon
Type	Heat Shrink End Cap
Shrink Ratio	3:1
Voltage Rating	600 V
Length	3 in ; 76.2 mm
Dielectric Strength	500 V/Mil (20kV/mm)
Volume Resistivity	1016 ohm-cm
Continuous Operating Temperature	-67 to +230 F ; -55 to +110 C
Minimum Shrink Temperature	248 F ; 120 C
Water Absorption	0.10%
Color	Black

### European Specifications (ETIM)

ETIM	EC000218 Heat-shrink end cap
Inner diameter before heat-shrink	27.94mm
Inner diameter after heat-shrink	8.89mm
Total length after shrink	0.0762mm

### Packaging

Inner Quantity	5
Outer Quantity	50
Outer Dimensions (inches)	13x6x13
Weight Uom	4 lbs. per 100

### Documents / Support Tools

Safety Data Sheet (SDS) Global	SDS-00046-TB2
--------------------------------	---------------