



Actual

Catalog Number: XR90G-23BR.50
Product ID: 7TAA292240R0325
UPC Number: 78620962247
EAN Number: 0763003028218
Status: Active

Very Flexible, Medium Duty Three Layer Corrugated Conduit - Conduit Size NW/Metric 23/25, Outer Layer Black, Intermediate Layer Yellow, Inner Layer Red, 50 Meters

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	PMA
Type	Medium Wall Conduit
Application	In Robotics and Automation Industry
Trade Size	NW23
Length	50 m
Radius	100 Millimeters
Flexibility	Very Flexible
Material	Polyamide 12
Color	Red, Yellow, Black

European Specifications (ETIM)

ETIM	EC001175 Corrugated plastic hose
Nominal diameter	25mm
Outer diameter	28.4mm
Inner diameter	22.6mm
Material	Polyamide 12
Compressive strength	130N
Operating temperature	-40 - +95°C
Fire resistance in accordance with UL94	HB
UV resistant	Y
Colour	Black
Sheathing material	Polyamide
Bending strength	Flexible
Lengthwise slotted	N
Closable (two-part)	N
Halogen free	Y
Approved according to DIN EN 61386-23	N
Approved according to UR	N
Approved according to CSA	N
Approved according to LUL/British Standard	N
Approved according to Lloyd's Register TA	N
Approved according to UTAC	N
Approved according to DIN 5510	N
Approved according to NF F 16-101	N

Packaging

Inner Quantity	1
Outer Quantity	10
Outer Dimensions (inches)	47.244x31.496x30.709
Weight Uom	16.4 lbs. Each

Documents / Support Tools

Video US	Available on Website
----------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

T&B Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com