

**Catalog Number:** XR90G-70BR.30  
**Product ID:** 7TCA292000R7414  
**UPC Number:** 78621006642  
**EAN Number:** 07630031202130  
**Status:** Active

Three Layer Corrugated Very Flexible, Medium-Duty Conduit, Size NW70/80 Metric, 150 Millimeter Static Radius, 350 Millimeter Dynamic Radius, Polyamide 12, Outer Layer Black, Intermediate Layer Yellow, Inner Layer Red

#### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	PMA
Type	Medium Wall Conduit
Application	In Robotics and Automation Industry
Trade Size	NW70
Length	30 m
Radius	350 Millimeters
Flexibility	Very Flexible
Material	Polyamide 12
Color	Red, Yellow, Black

#### European Specifications (ETIM)

ETIM	EC001175 Corrugated plastic hose
Nominal diameter	80mm
Outer diameter	79.8mm
Inner diameter	67.4mm
Material	Polyamide 12
Compressive strength	130N
Operating temperature	-40 - +95°C
Fire resistance in accordance with UL94	HB
UV resistant	Y
Colour	Black
Sheathing material	Polyamide
Bending strength	Flexible
Lengthwise slotted	N
Closable (two-part)	N
Halogen free	Y
Approved according to DIN EN 61386-23	N
Approved according to UR	N
Approved according to CSA	N
Approved according to LUL/British Standard	N
Approved according to Lloyd's Register TA	N
Approved according to UTAC	N
Approved according to DIN 5510	N
Approved according to NF F 16-101	N

#### Packaging

Inner Quantity	1
Outer Quantity	2
Outer Dimensions (inches)	45.669x45.669x26.378
Weight Uom	12.6 lbs. Each

#### Documents / Support Tools

Video US	Available on Website
----------	----------------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
860 Ridge Lake Blvd.  
Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)