



Catalog Number: 540-41131
Product ID: 7TAG009160R0000
UPC Number: 78621006816
EAN Number: 05414363009221
Status: A



Actual

Cable Tie, Gray Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 208mm (8.19 Inches), Width of 3.6mm (0.14 Inches), Thickness of 1.04mm (0.04 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds)

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	High Performance
Application	For Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications
Width	0.142 in ; 3.6 mm
Length	8.19 in ; 208 mm
Thickness	0.041 in ; 1.04 mm
Material	Polyamide/Nylon 6.6
Color	Gray
Lock Mechanism	Stainless Steel Barb
Tensile Strength	40 pounds ; 180 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	3.6mm
Length belt/tape/tie	208mm
Tie thickness	1.04mm
Min. holding force	180N
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	Y
Colour	Grey
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N

Packaging

Inner Quantity	100
Inner Dimensions (inches)	12x6x0
Outer Quantity	1000
Outer Dimensions (inches)	9.6x6.5x5.5
Weight Uom	6.25 lbs. per 1000