



Actual

Catalog Number: TC050X050A
Product ID: 7TAG009840R0003
UPC Number: 78621028093
EAN Number: 05414363057796
Status: A

Four-Way Adhesive Mini Mounting Base, Natural Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Length of 12.7mm (0.50 Inches), Width of 12.7mm (0.50 Inches), Height of 4.52mm (0.178 Inches), Slot Width of 5.59 (0.22 Inches), Self-Adhesive Mounting Method, Bulk Pack

- Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.
Number Of Entries	4
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Adhesive
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	12.7mm
Width	12.7mm
Height	4.52mm
Suitable for cable tie width to	3mm
Type of fastening	Self-adhesive
Material	Plastic
Material quality	Polyamide PA
Operating temperature	0-+65°C
Colour	Natural colour

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	12x3x10
Outer Quantity	5000
Outer Dimensions (inches)	9.5x5x15.25
Weight Uom	0.63 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US Available on Website