



Catalog Number: TC105
Product ID: 7TAG009840R0005
UPC Number: 78621082248
EAN Number: 05414363057895
Status: A



Actual

Aluminum Mounting Plate, for Temperatures up to 450 Degrees Celsius (842 F), Weather and Ultraviolet Resistant, Length of 25.4mm (1.0 Inches), Width of 13.2mm (0.519 Inches), Height of 3.8mm (0.149 Inches), Screw Mounting With #10 Screw, Bulk Pack

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Aluminum Plate
Mount Size	#10
Material	Aluminum
Mounting	Epoxy Glue (TC2PA)/Screw
Operating Temperature	-60 to +250 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	25.4mm
Width	13.2mm
Height	3.8mm
Suitable for cable tie width to	4.8mm
Type of fastening	Other
Material	Metal
Material quality	Aluminium
Operating temperature	-100--+450°C

Packaging

Outer Quantity	1000
Outer Dimensions (inches)	7.9x4.4x5.9
Weight Uom	0.01 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------