



Actual

Catalog Number: TC112-TB
Product ID: 7TAG009880R0004
UPC Number: 78621082258
EAN Number: 05414363058052
Status: A

Miniature Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 19.1mm (0.75 Inches), Width of 9.5mm (0.374 Inches), Height of 4.8mm (0.189 Inches), Fillister-Head Screw Mounting Method

- These miniature mounting bases are ideal for high-density packaging. Threaded insert permits screw to come from outside of mounting surface.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	These miniature mounting bases are ideal for high-density packaging. Threaded insert permits screw to come from outside of mounting surface.
Cable Size	0.19 in ; 4.82 mm
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	19.1mm
Width	4.8mm
Height	4.8mm
Suitable for cable tie width to	4.8mm
Type of fastening	Other
Diameter mounting hole	4.4mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

Packaging

Inner Quantity	1000
Outer Quantity	10000
Outer Dimensions (inches)	16.3x8.5x7.6
Weight Uom	1.25 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US Available on Website