



Actual

Catalog Number: TC121-TB
Product ID: 7TAG009860R0006
UPC Number: 78621083085
EAN Number: 05414363075028
Status: A

Push-In Premountable Clamp, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Width of 11.30mm (0.445 Inches), Height of 10.54mm (0.415 Inches), Clip In Mounting Method

- Snap-In Premountable base for securing wire bundles in cabinets maintains the attractive external appearance of the equipment housing - Snap-Cap.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Snap-In Mounting Base Cap
Special Features	Snap-In Premountable base for securing wire bundles in cabinets maintains the attractive external appearance of the equipment housing - Snap-Cap.
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Push Mount
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Width	11.3mm
Height	10.54mm
Suitable for cable tie width to	4.8mm
Type of fastening	With insert clip
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

Packaging

Inner Quantity	1000
Outer Quantity	10000
Outer Dimensions (inches)	16.2x8.4x7.8
Weight Uom	0.63 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------