



Actual

Catalog Number: TC140
Product ID: 7TAG009880R0005
UPC Number: 78621082271
EAN Number: 05414363058199
Status: A

Saddle Support Mounting Base, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length of 14.29mm (0.563 Inches), Width of 8.73mm (0.344 Inches), Height of 6.75mm (0.266 Inches), Mount with #4 Screw, Bulk Pack

- This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Saddle Support Base
Special Features	This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.
Mount Size	#4
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	14.29mm
Width	8.73mm
Height	6.75mm
Suitable for cable tie width to	2.4mm
Type of fastening	Other
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

Packaging

Inner Quantity	500
Inner Dimensions (inches)	12x5x1.25
Outer Quantity	5000
Outer Dimensions (inches)	15.9x8x6.7
Weight Uom	4.38 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------