



Actual

**Catalog Number:** TC141  
**Product ID:** 7TAG009880R0006  
**UPC Number:** 78621082272  
**EAN Number:** 05414363058205  
**Status:** A

Saddle Support Mounting Base, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length of 17.07mm (0.672 Inches), Width of 11.13mm (0.438 Inches), Height of 8.33mm (0.328 Inches), Screw Mounting Method, #6 Pan Head Screw, Bulk Pack

- This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.

**North American Specifications (UNSPSC)**

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Saddle Support Base
Special Features	This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.
Mount Size	#6
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

**European Specifications (ETIM)**

ETIM	EC000449 Mounting base and -element for cable ties
Length	17.07mm
Width	11.13mm
Height	8.33mm
Suitable for cable tie width to	2.4mm
Type of fastening	Other
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

**Packaging**

Inner Quantity	500
Inner Dimensions (inches)	15x12x3
Outer Quantity	5000
Outer Dimensions (inches)	16.5x8.95x7.5
Weight Uom	1.88 lbs. per 1000

**Documents / Support Tools**

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------