



Representative

**Project:** CABLE TIE MOUNTS  
**Location:** WILMINGTON

**STANDARD ELECTRIC SUPPLY**  
14 JEWEL DRIVE

**Catalog Number:** TC142X  
**Product ID:** 7TAG009840R0007  
**UPC Number:** 78620987440  
**EAN Number:** 05414363500278  
**Status:** A

Saddle Support Mounting Base, Heat Stabilized Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length of 23.42mm (0.922 Inches), Width of 14.29mm (0.563 Inches), Height of 10.72mm (0.422 Inches), Mount with #10 Screw, Bulk Pack

- This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.

#### North American Specifications (UNSPSC)

|                       |  |
|-----------------------|--|
| UNSPSC                | 39121717 Cable tie mounts  |
| IGCC                  | 5065 Cable tie mounts  |
| Type                  | Saddle Support Base  |
| Special Features      | This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner. |
| Material              | Nylon/Polyamide 6.6  |
| Color                 | Black  |
| Mounting              | Screw  |
| Operating Temperature | -40 to +185 F  |

#### European Specifications (ETIM)

|                                 |  |
|---------------------------------|--|
| ETIM                            | EC000449 Mounting base and -element for cable ties |
| Length                          | 23.42mm  |
| Width                           | 14.29mm  |
| Height                          | 10.72mm  |
| Suitable for cable tie width to | 7.6mm  |
| Type of fastening               | Other  |
| Material                        | Plastic  |
| Material quality                | Polyamide PA                                       |
| Operating temperature           | -40-+85°C  |
| Colour                          | Black  |

#### Packaging

|                           |                    |
|---------------------------|--------------------|
| Inner Quantity            | 500                |
| Inner Dimensions (inches) | 12x15x3            |
| Outer Quantity            | 5000               |
| Outer Dimensions (inches) | 18x13x13.5         |
| Weight Uom                | 1.25 lbs. per 1000 |

#### Documents / Support Tools

|                                   |                      |
|-----------------------------------|----------------------|
| Technical Drawing / Data Sheet US | Available on Website |
|-----------------------------------|----------------------|

