



Actual

Catalog Number: TC150X150A-L
Product ID: 7TAG009830R0002
UPC Number: 78621049296
EAN Number: 05414363162865
Status: A

Four-Way Mounting Base, Natural Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Length of 38.1mm (1.5 Inches), Width of 38.1mm (1.5 Inches), Height of 7.4mm (0.290 Inches), Self-Adhesive/Screw Mounting Method, #8 Screw, Mounting Hole Size of 4.3mm (0.169 Inches), 50 Pack

- Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.
Number Of Entries	4
Mount Size	#8
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Adhesive/Screw
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	38.1mm
Width	38.1mm
Height	7.4mm
Suitable for cable tie width to	7.9mm
Type of fastening	Stick and screw
Diameter mounting hole	4.3mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	0-+65°C
Colour	Natural colour

Packaging

Inner Quantity	50
Inner Dimensions (inches)	12x1x6
Outer Quantity	500
Outer Dimensions (inches)	12.9x11.1x5.8
Weight Uom	6.88 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------