



Representative

**Catalog Number:** HSC2-20  
**Product ID:** 7TAA017170R0000  
**UPC Number:** 78621087209  
**EAN Number:** 05414363152996  
**Status:** A

Heat-Shrinkable HSC Series End Caps for Cable Range 6 - 2 AWG, Expanded Diameter 3/4 inch, Length 2.5 inch, rated for 600 Volt, 90 degrees continuous use, Material: Cross-linked polyolefin with thermoplastic adhesive liner, Black

- Provides effective method for sealing cable ends, pipe conduit, etc. Extra thickness at the tip of the end prevents sharp ends of the cable from puncturing the seal.
- Resistant to common fluids and solvents.
- Adhesive liner provides complete environmental protection and insulation.

**North American Specifications (UNSPSC)**

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Heavy-Wall Heat Shrinkable Tubing
Special Features	Provides effective method for sealing cable ends, pipe conduit, etc. Extra thickness at the tip of the end prevents sharp ends of the cable from puncturing the seal.
Voltage Rating	600 V
Length	2.5 in ; 63.5 mm
Flammability	Flame Retardant
Color	Black

**European Specifications (ETIM)**

ETIM	EC000218 Heat-shrink end cap
Inner diameter before heat-shrink	19.05mm
Inner diameter after heat-shrink	6.096mm
Total length after shrink	0.0635mm

**Packaging**

Inner Quantity	10
Inner Dimensions (inches)	6.1x5.7x1.9
Outer Quantity	100
Outer Dimensions (inches)	8.4x8.3x8.7
Weight Uom	2.5 lbs. per 100

**Documents / Support Tools**

Technical Drawing / Data Sheet	WSD-000470
Instruction Sheet	TA01621-TB2
Safety Data Sheet (SDS) Global	SDS-00046-TB2