



Actual

**Catalog Number:** TC200X200A  
**Product ID:** 7TAG009840R0012  
**UPC Number:** 78621028101  
**EAN Number:** 05414363058311  
**Status:** A

Four-Way Mounting Base, Natural Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Length of 50.8mm (2.0 Inches), Width of 50.8mm (2.0 Inches), Height of 7.4mm (0.290 Inches), Self-Adhesive/Screw Mounting Method, #8 Screw, Mounting Hole Size of 4.3mm (0.169 Inches), Bulk Pack

- Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.

### North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Brand Name	Ty-Rap
Type	Mounting Base
Special Features	Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.
Number Of Entries	4
Mount Size	#8
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Adhesive/Screw
Operating Temperature	-40 to +185 F

### European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	50.8mm
Width	50.8mm
Height	7.4mm
Suitable for cable tie width to	7.9mm
Type of fastening	Stick and screw
Diameter mounting hole	4.3mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	0-+65°C
Colour	Natural colour

### Packaging

Inner Quantity	500
Inner Dimensions (inches)	22x3x14
Outer Quantity	2500
Outer Dimensions (inches)	20.25x14.75x18.5
Weight Uom	1.25 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US Available on Website