



Actual

**Catalog Number:** TC344  
**Product ID:** 7TAG009810R0008  
**UPC Number:** 78621098002  
**EAN Number:** 05414363058526  
**Status:** A

Four-Way Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 19mm (0.75 Inches), Width of 19mm (0.75 Inches), Height of 4.9mm (0.19 Inches), Two-Component Glue/Screw Mounting Method, Bulk Pack

- Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.

#### North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Epoxy Glue (TC2PA)/Screw
Operating Temperature	-40 to +185 F

#### European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	19.05mm
Width	19.05mm
Height	4.85mm
Suitable for cable tie width to	3.6mm
Type of fastening	Stick
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

#### Packaging

Inner Quantity	1000
Inner Dimensions (inches)	10x1x10
Outer Quantity	5000
Outer Dimensions (inches)	9.5x5x15.25
Weight Uom	1.25 lbs. per 1000

#### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------