



Actual

Catalog Number: TC344AX
Product ID: 7TAG009810R0012
UPC Number: 78621006876
EAN Number: 05414363058540
Status: A

Four-Way Adhesive Mounting Base, Black Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Weather and UV Resistant, Length of 19mm (0.75 Inches), Width of 19mm (0.75 Inches), Height of 4.9mm (0.19 Inches), Self-Adhesive Mounting Method, Bulk Pack

- Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.
Number Of Entries	4
Material	Nylon/Polyamide 6.6 Weather Resistant
Color	Black
Mounting	Self-Adhesive
Operating Temperature	-32 to +150 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	19.05mm
Width	19.05mm
Height	4.85mm
Suitable for cable tie width to	3.6mm
Type of fastening	Other
Material	Plastic
Material quality	Polyamide PA
Operating temperature	0-+65°C
Colour	Black

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	12x10x0
Outer Quantity	5000
Outer Dimensions (inches)	15.5x9.9x5.9
Weight Uom	1.25 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US Available on Website