



Actual

**Catalog Number:** TC345  
**Product ID:** 7TAG009820R0041  
**UPC Number:** 78621087100  
**EAN Number:** 05414363058557  
**Status:** A

Four-Way Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Height of 5.1mm (0.20 Inches), Screw Mounting Method, #6 Screw, Mounting Hole Size of 4.3mm (0.17 Inches), Bulk Pack

- Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.

### North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

### European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	28.58mm
Width	28.58mm
Height	5.08mm
Suitable for cable tie width to	5.2mm
Type of fastening	Other
Diameter mounting hole	4mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

### Packaging

Inner Quantity	1000
Inner Dimensions (inches)	20x14x0
Outer Quantity	5000
Outer Dimensions (inches)	21x13.4x9.5
Weight Uom	3.13 lbs. per 1000

### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000068
--------------------------------	------------