



Actual

Catalog Number: TC347A
Product ID: 7TAG009820R0051
UPC Number: 78621088848
EAN Number: 05414363058618
Status: A

Four-Way and Two-Way Mounting Base With Open Leg Design, Natural Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Height of 8.7mm (0.34 Inches), Self-Adhesive Mounting Method, Bulk Pack

- Accommodates 4-way for ties up to .091 and 2-way for ties up to .301 maximum width.

North American Specifications (UNSPSC)

| | |
|-----------------------|---|
| UNSPSC | 39121717 Cable tie mounts |
| IGCC | 5065 Cable tie mounts |
| Type | Mounting Base |
| Special Features | Accommodates 4-way for ties up to .091 and 2-way for ties up to .301 maximum width. |
| Number Of Entries | 4 |
| Mount Size | #8 |
| Material | Nylon/Polyamide 6.6 |
| Color | Natural |
| Mounting | Self-Adhesive |
| Operating Temperature | -32 to +150 F |

European Specifications (ETIM)

| | |
|---------------------------------|--|
| ETIM | EC000449 Mounting base and -element for cable ties |
| Length | 28.58mm |
| Width | 28.58mm |
| Height | 8.53mm |
| Suitable for cable tie width to | 7.6mm |
| Type of fastening | Self-adhesive |
| Material | Plastic |
| Material quality | Polyamide PA |
| Operating temperature | 0-+65°C |
| Colour | Natural colour |

Packaging

| | |
|---------------------------|--------------------|
| Inner Quantity | 1000 |
| Inner Dimensions (inches) | 20x14x0 |
| Outer Quantity | 5000 |
| Outer Dimensions (inches) | 21x13.4x9.5 |
| Weight Uom | 4.38 lbs. per 1000 |

Documents / Support Tools

| | |
|--------------------------------|------------|
| Technical Drawing / Data Sheet | WSD-000166 |
|--------------------------------|------------|