



Actual

Catalog Number: TC347FR
Product ID: 7TAG009820R0053
UPC Number: 78621090021
EAN Number: 05414363058625
Status: A

Four-Way and Two-Way Mounting Base With Open Leg Design, Flame Retardant Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Height of 8.7mm (0.34 Inches), Screw Mounting Method or Two-Component Glue, #8 Screw, Mounting Hole Size of 4.4mm (0.17 Inches), Bulk Pack

- Accommodates 4-way for ties up to .091 and 2-way for ties up to .301 maximum width.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Special Features	Accommodates 4-way for ties up to .091 and 2-way for ties up to .301 maximum width.
Material	Nylon/Polyamide 6.6 Flame Retardant
Color	Natural
Mounting	Epoxy Glue (TC2PA)/Screw
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	28.58mm
Width	28.58mm
Height	8.53mm
Suitable for cable tie width to	8.6mm
Type of fastening	Stick and screw
Diameter mounting hole	4.4mm
Material	Plastic
Material quality	Polyamide flame retardant
Operating temperature	-40-+85°C
Colour	Natural colour

Packaging

Inner Quantity	1000
Outer Quantity	5000
Outer Dimensions (inches)	21.1x10x13.7
Weight Uom	4.38 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000166
--------------------------------	------------