



Catalog Number: TC368A
Product ID: 7TAG009840R0016
UPC Number: 78621071224
EAN Number: 05414363058748
Status: A



Actual

Four-Way Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 50.8mm (2.0 Inches), Width of 50.8mm (2.0 Inches), Height of 6.6mm (0.260 Inches), Self-Adhesive/Screw Mounting Method, #8 Screw, Mounting Hole Size of 4.3mm (0.169 Inches)

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Mounting Base
Number Of Entries	4
Mount Size	#8
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Self-Adhesive/Screw
Operating Temperature	-32 to +150 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	50.8mm
Width	50.8mm
Height	6.6mm
Suitable for cable tie width to	20.1mm
Type of fastening	Stick and screw
Diameter mounting hole	4.3mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	0-+65°C
Colour	Natural colour

Packaging

Inner Quantity	500
Inner Dimensions (inches)	22x3x14
Outer Quantity	2500
Outer Dimensions (inches)	31.75x14.25x10.5
Weight Uom	1.13 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------