



Actual

Catalog Number: TC375
Product ID: 7TAG009910R0084
UPC Number: 78621082682
EAN Number: 05414363058779
Status: A

Stand-Off Brackets Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 92.71mm (3.65 Inches), Width of 17.5mm (0.69 Inches), Height of 19.05mm (0.75 Inches), Screw Mounting Method, Mounting Hole Diameter of 4.8mm (0.189 Inches)

- These brackets permit bundles to be mounted on either side. They also serve as means to raise bundles off the surface.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Type	Stand-Off Brackets
Special Features	These brackets permit bundles to be mounted on either side. They also serve as means to raise bundles off the surface.
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	92.71mm
Width	17.5mm
Height	19.05mm
Suitable for cable tie width to	4.8mm
Type of fastening	Other
Diameter mounting hole	4.8mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

Packaging

Inner Quantity	100
Outer Quantity	1000
Outer Dimensions (inches)	17.25x13.25x10.25
Weight Uom	1 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------